

METAL HALIDE LAMPS • DOUBLE ENDED

UMI & SMH SERIES


- High Brightness
- 5600K Daylight Color Temperature

Please see Safety and Handling Instructions on page 84.




Watts	Ushio Ordering Code	Ushio Lamp Code	Volts	Amps	Arc Gap	Dimensions mm			Luminous Flux lm	Color Temp K	Avg Life h	Base Type	Burn Position
						Dia (A)	LCL (B)	OAL (C)					
UMI Series – Double Ended Metal Halide													
575	5000250	• UMI-575/GS	95	7.0	7	21	115	145	49000	5600	750	SFc10-4 M4	Any
1200	5000235	UMI-1200/HB	100	13.8	7	21	115	145	110000	5600	750	SFc 10-4 M4	Any
1200	5000234	• UMI-1200/GS	100	13.8	10	27	180	220	110000	5600	750	SFc 15.5-6 0.5	Any
2500	5000241	• UMI-2500/GS	115	25.6	14	30	290	355	240000	5600	500	SFa 21-12	H±15°
4000	5000245	UMI-4000	200	24.0	34	38	340	405	410000	5600	500	SFa 21-12 ••	H±15°
6000	5000251	UMI-6000	125	55.0	20	52	—	450	650000	5600	300	25.4x50.8	H±15°
SMH Series – Double Ended Metal Halide													
300	5000962	SMH-300/A1 (HTI300W/DX)	95	3.6	5.5	17	—	92	22000	5600	1000	SFc10-4	H±15°


- Gap Short Version
- 165mm (x2) lead wire with 8mm diameter ring terminal




UMI-575/GS UMI-1200/GS, HB



UMI-2500/GS UMI-4000



UMI-6000



SMH-300/A1

(Hg) - LAMP CONTAINS MERCURY
Manage in Accord with Disposal Laws
See: www.lamprecycle.org